


# Rittal – The System.

Faster – better – everywhere.



## DK 5528.181

# TS IT Network/Server Enclosure

State: 6/21/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5528.181 - TS IT Network/Server Enclosure with vented door, with 19" mounting frame

TS IT, vented, for room climate control. 482.6 mm (19") interior installation with 482.6 mm (19") mounting frame for a load capacity of up to 1,500 kg, available in a range of size variants.

## Features

Model No.	DK 5528.181
Material	Carbon steel Aluminum
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated
General color	RAL 7035
Color	Housing frame and panels: RAL 7035 Interior installation, vent grille at the front: RAL 9005
Supply includes	Enclosure frame TS 8 with doors and roof plate Aluminum carbon steel door at the front, vented (vented surface area approx. 85% perforated), 180° hinges Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E Two 482.6 mm (19") mounting frames, front and rear, depth-variable Spacers, height 50 mm, for raising the cover plate above the fan breakout in the roof panel, for passive ventilation (enclosed) Not required for variants without cutout. Connection accessories for potential equalization with earthing point (supplied loose) 12 x 19" fasteners 1 U, contacting (supplied) 50 multi-tooth screws, conductive (supplied loose) IPPC pallet Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate Carbon steel door at the rear, vertically divided, vented (free area in perforated carbon steel part approx. 85 %), 180° hinges

# Features

---

Dimensions	Width: 600 mm Height: 1,800 mm Depth: 800 mm Width: 23.6 " Height: 70.9 " Depth: 31.5 "
Height units	38 U
Height units	38 U
Mounting space to 19" level, front/ rear	84 mm / 168 mm
Distance between levels as delivered	545 mm 21.5 "
Design doors	Vented
Design of 19" mounting level(s)	Mounting frame, 482.6 mm (19")
Load capacity	15,000 N
Note	The door-opening angle may vary depending on site requirements or applications
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	74.9 kg
Gross weight	82.6 kg
Customs tariff number	94032080
ETIM 9	EC002499
ECLASS 8.0	27180207
Product description	TS IT, 19" mounting frame, vented, WHD: 600 x 1800 x 800 mm, 38 U

---

# Approvals

---

Approvals	UL + C-UL (listed)
-----------	--------------------

---

# Approvals

---

Certificates

Surface finish

---

Explanations

Declaration of conformity