

Rittal – The System.

Faster – better – everywhere.



CP 6106.500 Pedestal, open

State: 7/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

CP 6106.500 - Pedestal, open

Open pedestal for retrospective cable entry with pre-assembled connectors.



Features

Model No.	CP 6106.500
Product description	The welded alternative to the pedestal, complete. For retrospective cable entry with pre-assembled connectors.
Material	Steel
Surface finish	Spray-finished
Color	RAL 7035
Width base plate	400 mm 15.7 "
Height base plate	10 mm 0.39 "
Depth base plate	400 mm 15.7 "
Material thickness pedestal	3 mm 0.12 "
Pedestal tube cross-section depth	73 mm 2.87 "
Pedestal tube cross-section width	86 mm 3.39 "

Features

Load capacity, static	40 kg 88.2 lb.
Dimensions	Height: 1,095 mm Height: 43.1 "
Packaging unit	1 pc(s).
Net weight	22.5 kg
Gross weight	22.691 kg
PCF/VE (cradle-to-gate)	91.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002534
ECLASS 8.0	27182604
Product description	CP Pedestal, open, CP 60, WHD: 400x1095x400 mm