
### Rittal – The System.

Faster – better – everywhere.





# CP 6206.850 Pivot

State: 11/9/2025 (Source: rittal.com/us-en)



### CP 6206.850 - Pivot with/without jib

For direct, pivoted integration into machines and systems.

#### **Features**

Model No.	CP 6206.850
Version	Pivot with jib
Product description	For direct, pivoted integration into machines and systems.
Benefits	With integral rotation range restrictor
Applications	Housing suspended or top-mounted
Color	RAL 7024/7035
Jib length	200 mm 7.87 ″
Installation options	To fit housings with Ø 130 mm support arm connection
Load capacity, static	700 N 157.366 lbf.
Rotation angle/swivel area	Approximately 310° The range of rotation can be limited by inserting the grub (set) screws provided
Packaging unit	1 pc(s).
Net weight	2.66
Gross weight	2.86
Customs tariff number	76169990
EAN	4028177707931
ETIM 9	EC002622
ECLASS 8.0	27189263

© Rittal 2025

## **Approvals**

Explanations

Manufacturer's declaration

© Rittal 2025 3