Rittal – The System.

Faster – better – everywhere.





ENCLOSURES

POWER DISTRIBUTION CLIMATE CONTROL

>> IT INFRASTRUCTURE >> SOFTWARE & SERVICES

CP 6206.870 - Pivot with/without jib

For direct, pivoted integration into machines and systems.

Features

Model No.	CP 6206.870	
Version	Pivot without jib	
Product description	For direct, pivoted integration into machines and systems.	
Benefits	With integral rotation range restrictor	
Applications	Housing suspended or top-mounted	
Color	RAL 7035	
Installation options	To fit housings with Ø 130 mm support arm connection	
Load capacity, static	700 N 157.366 lbf.	
Rotation angle/swivel area	Approximately 310° The range of rotation can be limited by inserting the grub (set) screws provided	
Packaging unit	1 pc(s).	
Net weight	1.36	
Gross weight	1.46	
Customs tariff number	76169990	
EAN	4028177707948	
ETIM 9	EC002622	
ECLASS 8.0	27189263	

Approvals

Explanations	Manufacturer's declaration	
--------------	----------------------------	--

© Rittal 2025