

Rittal – The System.

Faster – better – everywhere.



CP 6218.150

Support section CP 180

State: 8/27/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6218.150 - Support section CP 180 open

Attached to the connection components with 4 self-tapping screws in the screw channel. May be cut to any required length, no thread-tapping required. Open cable duct for easy servicing access and for pre-assembled cables with connectors, lockable via cover profile. X-shaped profiling for greater load capacity, large cable routing channels. Upper channel suitable for cables with large connectors (e.g. DVI or VGA) and available/usable throughout the entire system.

Features

| | |
|---------------------|--|
| Model No. | CP 6218.150 |
| Product description | Attached to the connection components with 4 self-tapping screws in the screw channel. May be cut to any required length, no thread-tapping required. Open cable duct for easy servicing access and for pre-assembled cables with connectors, lockable via cover profile. X-shaped profiling for greater load capacity, large cable routing channels. Upper channel suitable for cables with large connectors (e.g. DVI or VGA) and available/usable throughout the entire system. |
| Material | Support section: Extruded aluminum section Cover: Plastic |
| Color | Support section: RAL 7035 Cover: RAL 7024 |
| Supply includes | Support section Clip-in lid |
| Length | 500 mm 19.7 " |
| Dimensions | Width: 90 mm Height: 160 mm Length: 500 mm Width: 3.54 " Height: 6.3 " Length: 19.7 " |
| Packaging unit | 1 pc(s). |
| Net weight | 5.471 |

Features

| | |
|-----------------------|---------------|
| Gross weight | 5.759 |
| Customs tariff number | 76042100 |
| EAN | 4028177683839 |
| ETIM 9 | EC000882 |
| ECLASS 8.0 | 27400556 |

Approvals

| | |
|--------------|----------------------------|
| Explanations | Manufacturer's declaration |
|--------------|----------------------------|