


# Rittal – The System.

Faster – better – everywhere.



## CP 6315.200

## Operating housing with handle strips

State: 8/20/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6315.200 - Operating housing with handle strips

Command panel with handle strips in contemporary design of sheet steel, with Ø 130 mm support arm cut-out to fit CP 60/120/180 support arm system, service access optionally from the front or rear, aluminum front panel easily removable for machining, protection category IP 55



## Features

|                 |  |
|-----------------|--|
| Model No.       | CP 6315.200  |
| Material        | Housing and door: Carbon steel<br>Handle strips: Aluminum<br>Front panel: Aluminum<br>Cover caps: Plastic  |
| Surface finish  | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Handle strip: Natural anodized<br>Front panel: Natural anodized.   |
| Color           | Housing and door: RAL 7035<br>Handle strip: Natural anodized<br>Front panel: Natural anodized.<br>Cover caps: Similar to RAL 7024  |
| Supply includes | Housing with cut-out and reinforcement for support arm connection Ø 130 mm<br>Front with maximum cut-out, covered with easily machinable 3 mm aluminum front panel<br>Side handle strips and cover caps<br>Cam lock with 3 mm double-bit insert<br>Integral interior mounting bracket with TS system punchings |

# Features

|                                     |   |
|-------------------------------------|---|
| Dimensions                          | Width: 380 mm<br>Height: 300 mm<br>Depth: 210 mm<br>Width: 15 "<br>Height: 11.8 "<br>Depth: 8.27 "  |
| Protection category IP to IEC 60529 | IP 55   |
| Version                             | Service access from front   |
| Note                                | The support arm connection and door catch may be swapped over by rotating the enclosure<br>Optional: Support arm connection Ø 130 mm, preformed off-center in the reinforcement plate, easily drilled out<br>Lock systems for servicing access from the front: 41 mm lock inserts, type C, lock cylinder, plastic handles and T-handles, type C |
| Base material                       | Aluminum  |
| Note on Model No.:                  | Compatible mounting plate 5050.430 with shipping bag 5050.507   |
| Lock                                | Lock version: Sickle-shaped locking nose<br>No. of locks: 1<br>Lock Insert: 3 mm double-bit   |
| Packaging unit                      | 1 pc(s).  |
| Net weight                          | 7.955   |
| Gross weight                        | 8.374   |
| Customs tariff number               | 94032080  |
| EAN                                 | 4028177693944   |
| ECLASS 8.0                          | 27180505  |

## Approvals

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|