

# Rittal – The System.

Faster – better – everywhere.



## CP 6321.000

# Operating housing for desktop TFT up to 24"

State: 6/26/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6321.000 - Operating housing for desktop TFT up to 24"

Integrated VESA 75/100 mount. Effective and attractive protection for commercially available desktop TFTs up to 24" in 16:9/16:10 formats. High protection category of IP 65.

## Features

|                     |   |
|---------------------|---|
| Model No.           | CP 6321.000   |
| Version             | Viewing window with single-pane safety glass  |
| Product description | For the installation of standard, commercially available desktop TFTs with a screen diagonal of up to 24" in the formats 16:9/16:10   |
| Material            | Housing and door: Carbon steel<br>Handle strips: Aluminum<br>Cover caps: Plastic<br>Viewing window: Single-pane safety glass<br>TFT holder: Carbon steel  |
| Surface finish      | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Handle strip: Natural anodized  |
| Color               | Housing and door: RAL 7035<br>Handle strip: Natural anodized<br>Cover caps: Similar to RAL 7024   |
| Supply includes     | Housing with cut-out and reinforcement for support arm connection<br>Ø 130 mm<br>Viewing window<br>Holder for desktop TFT with VESA 75/100 locator<br>Side handle strips and cover caps<br>Rear door with r/h hinge<br>Cam lock with 3 mm double-bit insert |
| Dimensions          | Width: 650 mm<br>Height: 450 mm<br>Depth: 155 mm<br>Width: 25.6 "<br>Height: 17.7 "<br>Depth: 6.1 "   |

# Features

---

|                                     |  |
|-------------------------------------|--|
| Protection category IP to IEC 60529 | IP 65  |
| No. of locks                        | 1  |
| Note                                | The support arm connection and door catch may be swapped over by rotating the enclosure<br>Optional: Support arm connection Ø 130 mm, preformed off-center in the reinforcement plate, easily drilled out<br>Lock insert may be exchanged for 27 mm lock inserts, type A, lock cylinder, plastic handles and T-handles, type B |
| Base material                       | Aluminum   |
| Lock                                | Lock version: Cam<br>No. of locks: 1<br>Lock Insert: 3 mm double-bit   |
| Packaging unit                      | 1 pc(s).   |
| Net weight                          | 16.468 kg  |
| Gross weight                        | 17.335 kg  |
| Customs tariff number               | 94032080   |
| ECLASS 8.0                          | 27180505   |
| Product description                 | CP Operating housing for desktop TFT up to 24", WHD: 650x450x155 mm, Sheet steel, handle strips made of aluminum   |

# Approvals

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|