Rittal - The System.

Faster – better – everywhere.






CP 6538.010 Command panel housing with door

State: 11/4/2025 (Source: rittal.com/us-en)



CP 6538.010 - Command panel housing with door Stainless steel

Operating door for enclosure made from stainless steel 1.4301, (AISI 304) with handle strips made from food-grade plastic. Can be combined with CP40 support arm system, stainless steel.



Features

Model No.	CP 6538.010
Version	With support arm connection CP 40, stainless steel
Material	Housing and door: Stainless steel 1.4301 (AISI 304) Handle strips: Plastic approved for use with foodstuffs, dyed blue
Surface finish	Brushed, grain 400
General color	Stainless steel
Color	Handle strips: Similar to RAL 5002
Supply includes	Housing of all-round solid construction Cut-out and reinforcement for support arm system CP 40 stainless steel Fastener with guide plate Door with sealing frame and side handle strips Lock: 3 mm double-bit

© Rittal 2025 2

Features

Dimensions	Width: 400 mm
	Height: 400 mm
	Depth: 150 mm
	Width: 15.7 ″ Height: 15.7 ″
	Protection category IP to IEC 60 529
Protection category NEMA	NEMA 12
Note	The support arm connection and door catch may be swapped over
	by rotating the enclosure
	3 mm double-bit lock insert may be exchanged for 41 mm lock
	inserts, plastic handles and T handles, type C
Base material	Stainless steel 1.4301 (AISI 304)
Note on Model No.:	Compatible mounting plate 5050.453 with shipping bag 5050.507
Packaging unit	1 pc(s).
Net weight	8.84
Gross weight	8.85
Customs tariff number	94032080
EAN	4028177220386
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals	UL
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3