Rittal - The System.

Faster – better – everywhere.





TP 6704.600 **Pedestals**

State: 11/17/2025 (Source: rittal.com/us-en)



TP 6704.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

Features

Model No.	TP 6704.600
Material	Housing: Carbon steel, 1.5 mm
	Door and console lid: Carbon steel, 2.0 mm, all-round foamed-in PU
	seal
	Mounting plate: Carbon steel
Surface finish	Housing, cover and door: Dipcoat-primed, powder-coated on the
	outside, textured paint
	Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing open at top
	Door or double door with locking rod (with depth 400 mm at the
	front, with depth 500 mm at the front and rear)
	Mounting panel
	Base Plates
Dimensions of mounting plate (W	499 mm x 571 mm
x H)	19.6 ″ x 22.5 ″
Number of doors	1
Dimensions	Width: 600 mm
	Height: 675 mm
	Depth: 500 mm
	Width: 23.6 "
	Height: 26.6 ″
	Depth: 19.7 "
Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Note	Mounting plate, depth variable in 25 mm increments

© Rittal 2025

Features

Packaging unit	1 pc(s).
Net weight	42.6
Gross weight	45
Customs tariff number	94032080
EAN	4028177959880
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3