Rittal - The System.

Faster – better – everywhere.





TP 6705.600 **Pedestals**

State: 12/14/2025 (Source: rittal.com/us-en)



TP 6705.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

Features

TP 6705.600
Housing: Carbon steel, 1.5 mm Door and console lid: Carbon steel, 2.0 mm, all-round foamed-in PU seal
Mounting plate: Carbon steel
Housing, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint
Mounting panel: Zinc-plated
RAL 7035
Housing open at top
Door or double door with locking rod (with depth 400 mm at the
front, with depth 500 mm at the front and rear)
Mounting panel
Base Plates
699 mm x 571 mm
27.5 ″ x 22.5 ″
1
Width: 800 mm
Height: 675 mm
Depth: 500 mm
Width: 31.5 "
Height: 26.6 "
Depth: 19.7 "
IP 55
NEMA 12
Mounting plate, depth variable in 25 mm increments

© Rittal 2025

Features

Packaging unit	1 pc(s).
Net weight	51
Gross weight	52.5
Customs tariff number	94032080
EAN	4028177959897
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3