

# Rittal – The System.

Faster – better – everywhere.



## TP 6706.600 Pedestals

State: 12/8/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TP 6706.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

## Features

Model No.	TP 6706.600
Material	Housing: Carbon steel, 1.5 mm Door and console lid: Carbon steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Carbon steel
Surface finish	Housing, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing open at top Door or double door with locking rod (with depth 400 mm at the front, with depth 500 mm at the front and rear) Mounting panel Base Plates
Dimensions of mounting plate (W x H)	1,099 mm x 571 mm 43.3 " x 22.5 "
Number of doors	2
Dimensions	Width: 1,200 mm Height: 675 mm Depth: 500 mm Width: 47.2 " Height: 26.6 " Depth: 19.7 "
Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Note	Mounting plate, depth variable in 25 mm increments

# Features

Packaging unit	1 pc(s).
Net weight	72
Gross weight	73
Customs tariff number	94032080
EAN	4028177959903
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK