

Rittal – The System.

Faster – better – everywhere.



CX 6742.000

CX One-Piece Console

State: 7/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CX 6742.000 - CX One-Piece Console

One-piece console for operating and monitoring, with large mounting plate and a high protection category of IP 55, available in four different widths.



Features

| | |
|-----------------|--|
| Model No. | CX 6742.000 |
| Version | One-piece consoles |
| Material | Housing: Carbon steel, 1.5 mm Door and console lid: Carbon steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Carbon steel, 2.5 mm |
| Surface finish | Housing, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Housing, solid back and sides Door or double door at front, with 3-point locking system Mounting panel Cover with cam locks, hinged at rear, 2 stays with automatic locking. Unlocking automatically on the left, manually on the right. Gland plate Lock: 3 mm double-bit |
| Dimensions | Width: 1,200 mm Height: 970 mm Depth: 400 mm Width: 47.2 " Height: 38.2 " Depth: 15.7 " |

Features

| | |
|--------------------------------------|--|
| Dimensions of mounting plate (W x H) | 1,120 mm x 900 mm 44.1 " x 35.4 " |
| Top depth | 495 mm 19.5 " |
| Bottom depth | 400 mm 15.7 " |
| Number of doors | 2 |
| IK code | IK10 |
| Protection category IP to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 1 NEMA 12 |
| Base material | Carbon steel |
| Dimensions | Width: 1,200 mm Height: 970 mm Top depth: 495 mm Bottom depth: 400 mm Width: 47.2 " Height: 38.2 " Top depth: 19.5 " Bottom depth: 15.7 " |
| Packaging unit | 1 pc(s). |
| Net weight | 83 kg |
| Gross weight | 86.75 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |
| Product description | CX one-piece console, WHD: 1200x970x400 mm, carbon steel |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
