



Rittal – The System.


Faster – better – everywhere.



DK 7000.620

Component Shelf, Static Installation


State: 2/17/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP

DK 7000.620 - Component Shelf, Static Installation for TE

The component shelf is attached directly to the front and rear 482.6 mm (19") mounting frame, load capacity: 30 kg.



Features

Model No.	DK 7000.620
Product description	The component shelf is attached at the side directly to the front and rear 482.6 mm (19") mounting frame for TE.
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 7035
Supply includes	Assembly components
Distance between mounting levels	495 mm 19.5 "
Load capacity static	300 N 67.443 lbf.
Note	Not suitable for combination with telescopic slides.
Contact surface	Width: 505 mm Depth: 410 mm Width: 19.9 " Depth: 16.1 "

Features

Dimensions	Width: 511 mm Height: 22 mm Depth: 413 mm Width: 20.1 " Height: 0.87 " Depth: 16.3 "
Packaging unit	1 pc(s).
Net weight	3.25
Gross weight	3.7
Customs tariff number	94039910
EAN	4028177436411
ETIM 9	EC002620
ECLASS 8.0	27189261