

Rittal – The System.

Faster – better – everywhere.



DK 7044.130 Complete system CAT 6

State: 6/22/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7044.130 - Complete system CAT 6 for Network Cable Organizer

The Network Cable Organizer complete system revolutionizes structured cabling in all network racks from a depth of 800 mm. Excess lengths of cable - whether CAT 6 or fiber optic - are simply retracted by means of a spring balancer.



Features

Model No.	DK 7044.130
Product description	Modern network infrastructures rely on maximum performance and the greatest possible flexibility in cabling. A useful component here is the Network Cable Organizer (NCO). The robust 1 U mounting frame is pre-configured with 24 cable cassettes and revolutionizes conventional structured cabling with 8 times faster installation.
Benefits	<p>Minimize cable chaos—Prevent obstructions to the air circulation in the area of the network switches</p> <p>Always the right length: Surplus cable lengths—whether CAT 6 or fiber optic—are simply withdrawn with a spring balancer</p> <p>Each cable is 100% tested and supplied with the appropriate measurement record</p> <p>Front access – Ideal for retrofitting into racks with a depth of 800 mm or more</p>
Technical specifications	<p>CAT 6 cable STP</p> <p>2 x RJ 45 connectors per cable</p> <p>shielded RJ 45 connector with gold-plated pins</p> <p>Useable cable length per cassette: 1.6 m</p> <p>ISO/IEC 11801:2002, AWG 36, 100% copper, 250 MHz</p>
Applications	Can be used in all network racks from a depth of 800 mm

Features

Function principle	Attachment to front and rear 19" plane
Material	Mounting frame: carbon steel Box type plug-in units: Stainless steel, plastic (POM)
Color	Mounting frame: RAL 9005 Cable: red
Supply includes	Complete system CAT 6 24 CAT 6 cassettes Installation kit Assembly components
Number cassettes max	24
Number cassettes preassembled	24
Dimensions	Width: 450 mm Height: 44 mm Depth: 600 mm Width: 17.7 " Height: 1.73 " Depth: 23.6 "
Operating temperature range	10 °C...45 °C 50 °F...113 °F
Ambient humidity (non-condensing)	95 %
Relative humidity (non-condensing)	10 %
Packaging unit	1 pc(s).
Customs tariff number	73269098
EAN	4028177917231
ECLASS 8.0	27189265