
Rittal – The System.

Faster – better – everywhere.



DK 7072.200

Brush strip

State: 11/9/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7072.200 - Brush strip

Cut-outs for cable entry at any position in the side panel, rear panel, doors, roof and base plate can be attractively finished off by simply attaching the brush strip.

Features

Model No.	DK 7072.200
Product description	For individual expansion of enclosure panels, flange plates and panels. Cut-outs for cable entry at any position in the side panel, rear panel, doors, roof and base plate can be attractively finished off by simply attaching the brush strip.
Benefits	Snap-on surface: 10 mm
Function principle	Maximum cut-out height: 38 mm
Material	Plastic sheathing: 18 mm Brush strip: Plastic, UL 94-HB
Bristle length	30 mm 1.18 ″
Length	2 m 78.7 ″
Dimensions	Length: 2 m Length: 78.7 ″
For material thicknesses	0.6 - 1.5 mm 0.02 - 0.06 ″
Packaging unit	1 pc(s).
Net weight	0.43 kg
Gross weight	0.433 kg
Customs tariff number	96035000
ETIM 9	EC012298
ECLASS 8.0	27142421
Product description	DK brush strip, L: 2 m, bristle length: 30 mm, for sheet thickness: 0.6-1.5 mm