

Rittal – The System.

Faster – better – everywhere.



DK 7094.110 Fastening Screws

State: 9/11/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7094.110 - Fastening Screws

For slide-in electronic equipment, 482.6 mm (19") installed components and blanking plates.

Features

Model No.	DK 7094.110
Version	Cheese-head screw
Product description	For slide-in electronic equipment, 482.6 mm (19") installed components and blanking plates.
Supply includes	Incl. plastic washers
Mounting tip	Maximum tightening torque 3 Nm
Dimensions	Thread: M6 Thread length: 16 mm Thread: M6 Thread length: 0.63 "
Packaging unit	50 pc(s).
Net weight	0.2
Gross weight	0.28
Customs tariff number	73181900
EAN	4028177663022
ETIM 9	EC000889
ECLASS 8.0	23110190