


Rittal – The System.

Faster – better – everywhere.



DK 7109.200

Light, 1 U

State: 12/20/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7109.200 - Light, 1 U

Ready-to-connect light for installation in a 482.6 mm (19") level. Fluorescent Tubes, 8 kW, 230 V, 50 Hz

Features

Model No.	DK 7109.200
Product description	Ready-to-connect light for installation in 482.6 mm (19") mounting angles. Can also be fastened to the 25 mm system punchings using the long slot.
Material	Aluminum, anodized Plastic
Supply includes	Light, 1 U Light (bulb) Connection cable with grounding-pin plug Assembly components
Rated power	8 W
Length of connection cable	2.5 m 98.4 "
Connection options	Integrated connection cable with grounding type plug
Light (bulb)	Fluorescent tubes
Switch (type)	Integral, on/off
Rated impulse withstand voltage, phase to earth	1000 V AC
Rated impulse withstand voltage, phase to phase	500 V AC
Rated insulation voltage	500 V DC/1s
Dimensions	Width: 482.6 mm Width: 19 "
Rated operating voltage	230 V, 1~, 50 Hz
Packaging unit	1 pc(s).

Features

Net weight	1.05
Gross weight	1.193
Customs tariff number	94054990
EAN	4028177305557
ECLASS 8.0	27189241

Approvals

Approvals	TÜV
Explanations	Declaration of conformity