

Rittal – The System.

Faster – better – everywhere.



DK 7111.224

Cable routing bars, 19" attachment

State: 6/1/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7111.224 - Cable routing bars, 19" attachment

For structured routing of entire cable bundles, 19" attachment, connection comb.



Features

Model No.	DK 7111.224
Product description	For structured routing of bundled cables. The cable routing bars may be secured in a variety of different positions inside the enclosure.
Applications	For horizontal cable routing within the distributor level. Our unique open mounting hole design allows installation of the cable routing bars through the 19" mounting rails with the mounting screws of the installed components.
Material	Support: Carbon steel Cable routing bars, connection combs: Plastic UL 94-V0
Color	RAL 9005
Supply includes	Cable Routing Bars Connection combs
Number connection combs	2
Note	Size of individual chambers (HxD) approx. 34 x 100 mm
Height units	4 U
Packaging unit	4 pc(s).
Net weight	0.6 kg

Features

Gross weight	0.727 kg
PCF/VE (cradle-to-gate)	2.8 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC000322
ECLASS 8.0	27400604
Product description	DK Cable routing bars, 482.6 mm (19") attachment, 4 U
