

Rittal – The System.

Faster – better – everywhere.



DK 7111.300 Snap-in cable routing

State: 4/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7111.300 - Snap-in cable routing

For tool-less quick assembly in two versions: snap-in and twist-in.



Features

Model No.	DK 7111.300
Version	for snapping in
Benefits	The cable routing clip can be adjusted in diameter to match the guided cable cross-section
Material	Polyamide 6.6, self-extinguishing to UL 94-V2
Color	Natural
Cable entry	Min. cable diameter: 14 mm Max. cable diameter: 19 mm Min. cable diameter: 0.55 " Max. cable diameter: 0.75 "
For system punchings with Ø	6.2 mm 0.24 "
Min. cable diameter	14 mm 0.55 "
Max. cable diameter	19 mm 0.75 "

Features

Packaging unit	10 pc(s).
Net weight	0.03 kg
Gross weight	0.043 kg
Customs tariff number	39269097
ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	DK snap-in cable guide, for snap-in mounting without tools, for Ø max. 19 mm, polyamide, natural