
# Rittal - The System.

Faster – better – everywhere.





# DK 7113.000 Ground rail, horizontal

State: 11/18/2025 (Source: rittal.com/us-en)



# DK 7113.000 - Ground rail, horizontal for AX, VX, VX IT, TS, TS IT

Equipotential bonding strips, current carrying capacity approx. 200 A.

#### **Features**

Model No.	DK 7113.000
Supply includes	Ground rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, 15
	x 5 mm
	20 connection points with M5 screws
	2 ground connections 25 mm²
	2 isolators
	Assembly components
Dimensions	Width: 15 mm
	Height: 5 mm
	Length: 450 mm
	Width: 0.59 "
	Height: 0.2 "
	Length: 17.7 "
Suitable for	Enclosure type: AX
	VX
	VX IT
	TS
	TS IT
	AX wall-mounted housing, 3-part
	Width: > 600 mm
	Depth: > 600 mm
	Suitable for width/depth: 800 mm
	Enclosure type: AX
	VX
	VXIT
	TS
	TS IT
	AX wall-mounted housing, 3-part
	Width: > 23.6 "
	Depth: > 23.6 "
	Suitable for width/depth: 31.5 ″

© Rittal 2025

### Features

Packaging unit	1 pc(s).
Net weight	0.402
Gross weight	0.436
Customs tariff number	74198090
EAN	4028177124943
E-Number Sweden	E7239683
ETIM 9	EC000329
ECLASS 8.0	27400605

# **Approvals**

Explanations Manufacturer's declaration

© Rittal 2025 3