


Rittal – The System.

Faster – better – everywhere.



DK 7113.000

Ground rail, horizontal

State: 2/11/2026 (Source: ittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7113.000 - Ground rail, horizontal for AX, VX, VX IT, TS, TS IT

Equipotential bonding strips, current carrying capacity approx. 200 A.

Features

Model No.	DK 7113.000
Supply includes	Ground rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, 15 x 5 mm 20 connection points with M5 screws 2 ground connections 25 mm ² 2 isolators Assembly components
Dimensions	Width: 15 mm Height: 5 mm Length: 450 mm Width: 0.59 " Height: 0.2 " Length: 17.7 "
Suitable for	Enclosure type: AX VX VX IT TS TS IT AX wall-mounted housing, 3-part Width: > 600 mm Depth: > 600 mm Width/depth: 800 mm Enclosure type: AX VX VX IT TS TS IT AX wall-mounted housing, 3-part Width: > 23.6 " Depth: > 23.6 " Width/depth: 31.5 "

Features

Packaging unit	1 pc(s).
Net weight	0.402
Gross weight	0.436
Customs tariff number	74198090
EAN	4028177124943
E-Number Sweden	E7239683
ETIM 9	EC000329
ECLASS 8.0	27400605

Approvals