


**Rittal – The System.**

Faster – better – everywhere.



# DK 7113.000

## Ground rail, horizontal

State: 5/21/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7113.000 - Ground rail, horizontal for AX, VX, VX IT, TS, TS IT

Equipotential bonding strips, current carrying capacity approx. 200 A.

## Features

Model No.	DK 7113.000
Supply includes	Ground rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, 15 x 5 mm 20 connection points with M5 screws 2 ground connections 25 mm <sup>2</sup> 2 isolators Assembly components
Dimensions	Width: 15 mm Height: 5 mm Length: 450 mm Width: 0.59 " Height: 0.2 " Length: 17.7 "
Suitable for	Enclosure type: AX VX VX IT TS TS IT AX wall-mounted housing, 3-part Width: > 600 mm Depth: > 600 mm Width/depth: 800 mm Enclosure type: AX VX VX IT TS TS IT AX wall-mounted housing, 3-part Width: > 23.6 " Depth: > 23.6 " Width/depth: 31.5 "

# Features

---

Packaging unit	1 pc(s).
Net weight	0.402 kg
Gross weight	0.436 kg
Customs tariff number	74198090
ETIM 9	EC000329
ECLASS 8.0	27400605
Product description	DK earthing rail, horizontal, length 450 mm, W/D: >600 mm

# Approvals

---

Explanations	Manufacturer's declaration
--------------	----------------------------