

Rittal – The System.

Faster – better – everywhere.



DK 7119.140

**Component Shelf 1 U, Static
Installation**

State: 12/7/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7119.140 - Component Shelf 1 U, Static Installation

482.6 mm (19") system punchings

482.6 mm (19")/535 mm (metric), support surface for small active components such as modems or mini-hubs in 19" or metric levels: 10 kg.



Features

| | |
|---------------------|---|
| Model No. | DK 7119.140 |
| Version | 482.6 mm (19") version |
| Product description | The ideal support surface for small active components such as modems or mini-hubs. |
| Material | Carbon steel |
| Color | RAL 7035 |
| Load capacity | 10 kg surface load, static |
| Note | Not suitable for combination with telescopic slides. Free installation height inside the U approx. 35 mm |
| Dimensions | Width: 482.6 mm Depth: 140 mm Width: 19 " Depth: 5.51 " |
| Packaging unit | 1 pc(s). |
| Net weight | 0.781 |
| Gross weight | 0.881 |

Features

| | |
|-------------------------------------|--|
| PCF/VE (cradle-to-gate) | 3.2 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |
| EAN | 4028177221444 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |