
Rittal – The System.

Faster – better – everywhere.



# DK 7119.400

# Component Shelf 2 U, Static Installation


State: 11/21/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# DK 7119.400 - Component Shelf 2 U, Static Installation

Component shelves 2 U, fixed, for attachment to 19" system punchings. Load capacity: 25 kg.





## Features

| | |
|---|---|
| Model No. | DK 7119.400 |
| Version | 19" |
| Product description | Mounted on vertical 482.6 mm (19") rails. |
| Material | Carbon steel |
| Surface finish | Spray-finished |
| Color | RAL 7035 |
| Load capacity | 25 kg surface load, static |
| Note | Not suitable for combination with telescopic slides. |
| Dimensions | Width: 482.6 mm<br>Depth: 400 mm<br>Width: 19 ″<br>Depth: 15.7 ″ |
| Height units | 2 U |
| Packaging unit | 1 pc(s). |
| Net weight | 3.19 kg |
| Gross weight | 3.58 kg |
| PCF/VE (cradle-to-gate) | 12.9 kg CO2 eq (Cat B) |

© Rittal 2026

# Features

| | |
|---|---|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Component shelf, WHD: 482,6x2 Ux400 mm, 25 kg, static, distance between levels:, static installation, For 482.6 mm (19") system punchings, RAL 7035 |