

**Rittal – The System.**

Faster – better – everywhere.



# DK 7163.565

## Cable support

State: 6/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7163.565 - Cable support hinged, with anti-kink device and clamp

Kink-free cable routing in the desk unit using mobile chain links, can be released from both sides using the quick-release fastener.



## Features

Model No.	DK 7163.565
Product description	For secure routing of connection cables from the component shelf with telescopic pull-out to the clamping point. Kink-free cable routing in the desk unit using mobile chain links. Can be released from both sides using the quick-release fastener.
Material	Carbon steel, zinc-plated Desk unit: Plastic
Supply includes	Assembly components
Note	Max. depth of component shelves = Enclosure depth - 200 mm
Suitable for	Depth: > 600 mm Depth: > 23.6 "
Packaging unit	1 pc(s).
Net weight	0.7 kg
Gross weight	0.78 kg
PCF/VE (cradle-to-gate)	2.8 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098

# Features

---

ETIM 9	EC000322
ECLASS 8.0	27400604
Product description	DK Cable support, kink-free, For D: > 600 mm, Max. depth component shelf = depth rack-200 mm

---