
### Rittal - The System.

Faster – better – everywhere.





### DK 7165.035

# Component Shelf for Frame Attachment

State: 12/11/2025 (Source: rittal.com/us-en)



## DK 7165.035 - Component Shelf for Frame Attachment for cabinet width 600 mm, 800 mm

For installation in cabinets without 482.6 mm (19") mounting.

#### **Features**

Model No.	DK 7165.035
Version	Slotted
Product description	For frame attachment, installed in enclosures without 482.6 mm (19") accommodation.
Benefits	Mounting bolts or mounting rails may be installed on a 25 mm hole pattern in the enclosure depth  Mounting hole for handles provided.
Applications	For installing in enclosures without 482.6 mm (19") feature
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 7035
Supply includes	Component shelf, slotted 4 pc(s), fixing bolts
Installation options	Static installation: Component shelf, 50 kg with fixing bolts on punched section without mounting flange Static installation: Component shelf, 100 kg with mounting rails on punched sections without mounting flange Depth variable: device base with telescopic rails on mounting chassis
Load capacity	50 kg surface load
Mounting tip	Two system chassis are also required for the inner mounting level
Note	Max. depth of component shelves = Enclosure depth - 100 mm.

© Rittal 2025 2

### **Features**

Dimensions	Width: 471 mm
	Height: 29 mm
	Depth: 500 mm
	Width: 18.5 "
	Height: 1.14 "
	Depth: 19.7 "
Suitable for	Enclosure type: VX
	VX IT
	TSIT
	Width: 600 mm
	Enclosure type: VX
	VX IT
	TS IT
	Width: 23.6 "
Packaging unit	1 pc(s).
Net weight	2.78
Gross weight	2.98
PCF/VE (cradle-to-gate)	12.1 kg CO2 eq (Cat B)
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on
class	the basis of the product weight and self-declared
	<u> </u>
Customs tariff number	94039910
EAN	4028177165809
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3