

**Rittal – The System.**

Faster – better – everywhere.



**DK 7165.035**

# Component Shelf for Frame Attachment

State: 6/18/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7165.035 - Component Shelf for Frame Attachment for cabinet width 600 mm, 800 mm

For installation in cabinets without 482.6 mm (19") mounting.

## Features

|                      |   |
|----------------------|---|
| Model No.            | DK 7165.035   |
| Version              | Slotted   |
| Product description  | For frame attachment, installed in enclosures without 482.6 mm (19") accommodation.   |
| Benefits             | Mounting bolts or mounting rails may be installed on a 25 mm hole pattern in the enclosure depth<br>Mounting hole for handles provided.   |
| Applications         | For installing in enclosures without 482.6 mm (19") feature   |
| Material             | Carbon steel  |
| Surface finish       | Spray-finished  |
| Color                | RAL 7035  |
| Supply includes      | Component shelf, slotted<br>4 pc(s), fixing bolts   |
| Installation options | Static installation: Component shelf, 50 kg with fixing bolts on punched section without mounting flange<br>Static installation: Component shelf, 100 kg with mounting rails on punched sections without mounting flange<br>Depth variable: device base with telescopic rails on mounting chassis |
| Load capacity        | 50 kg surface load  |
| Mounting tip         | Two system chassis are also required for the inner mounting level   |
| Note                 | Max. depth of component shelves = Enclosure depth - 100 mm.   |

# Features

|                                     |  |
|-------------------------------------|--|
| Dimensions                          | Width: 471 mm<br>Height: 29 mm<br>Depth: 500 mm<br>Width: 18.5 "<br>Height: 1.14 "<br>Depth: 19.7 "                  |
| Suitable for                        | Enclosure type: VX<br>VX IT<br>TS IT<br>Width: 600 mm<br>Enclosure type: VX<br>VX IT<br>TS IT<br>Width: 23.6 "       |
| Packaging unit                      | 1 pc(s).   |
| Net weight                          | 2.78 kg  |
| Gross weight                        | 2.98 kg  |
| PCF/VE (cradle-to-gate)             | 12.1 kg CO2 eq (Cat B)   |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number               | 94039910   |
| ETIM 9                              | EC002620   |
| ECLASS 8.0                          | 27189261   |
| Product description                 | DK Component shelf, WHD: 471x29x500 mm, 50 kg, Slotted, For W: 600 mm, RAL 7035                                      |