


Rittal – The System.

Faster – better – everywhere.



DK 7241.500

Fiber-optic breakout box, 1 U

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7241.500 - Fiber-optic breakout box, 1 U

To accommodate splicing cassettes, for splice-free cabling of fiber optic breakout cables.

Features

Model No.	DK 7241.500
Product description	For splice-free cabling of fiberoptic breakout cables. Wiring harnesses can be fastened to the rear T-heads. Four self-adhesive cable clips are included in the box for cable routing and to store excess lengths of cable.
Material	Carbon steel
Color	RAL 7035
Supply includes	Breakout box Cable routing clips Mounting accessories for patch panel
Installation depth	250 mm 9.84 "
Height units	1 U
Packaging unit	1 pc(s).
Net weight	1.5 kg
Gross weight	1.684 kg
Customs tariff number	94032080
ETIM 9	EC001129
ECLASS 8.0	19170113
Product description	DK Fibre-optic breakout box, 1 U, For D: 250 mm