

Rittal – The System.

Faster – better – everywhere.



DK 7280.100 Service socket

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7280.100 - Service socket for enclosure frame attachment

Service outlet for enclosure frame attachment/16 A, integration of a service outlet within a separate supply circuit, independently of the IT network and UPS.



Features

Model No.	DK 7280.100
Product description	Integration of a service outlet within a separate supply circuit, independently of the IT network and UPS. Easy installation, fastened to housing frame with mounting bracket.
Material	Angle bracket: Carbon steel Socket: Plastic
Surface finish	Angle bracket: Zinc-plated
Supply includes	Angle bracket Damp-proof socket (IP 44) Fasteners
Rated voltage	230 V
Rated current (max.)	16 A
Outlets	D, ground pin (type F, CEE 7/3)
Packaging unit	1 pc(s).
Net weight	0.44 kg
Gross weight	0.472 kg
PCF/VE (cradle-to-gate)	1.8 kg CO2 eq (Cat B)

Features

Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	83024900
ETIM 9	EC000330
ECLASS 8.0	27142604
Product description	DK Service socket, CEE 7/3 (type F), 1-way, 16 A, For enclosure frame attachment
