

Rittal – The System.

Faster – better – everywhere.



DK 7282.035 Drawer

State: 6/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7282.035 - Drawer for a 482.6 mm (19") mounting level

Mounted on the front of profile rails, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts.



Features

Model No.	DK 7282.035
Product description	Mounted on the front of 482.6 mm (19") profile rails. Drawer includes cover and telescopic slides and can accommodate operating manuals and small parts. The smaller 2 U version is also suitable for mounting in a pivoting frame.
Material	Carbon steel
Color	RAL 7035
Supply includes	Fully assembled Security lock 12321
Clearance depth	419 mm 16.5 "
Clearance width	411 mm 16.2 "
Packaging unit	1 pc(s).
Net weight	6.435 kg
Gross weight	6.82 kg
PCF/VE (cradle-to-gate)	25.8 kg CO2 eq (Cat B)

Features

Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Drawer, 2 U, For a 482.6 mm (19") attachment level, Installation depth: 427 mm