
## Rittal - The System.

Faster - better - everywhere.





State: 11/15/2025 (Source: rittal.com/us-en)



## DK 7391.000 - Data Rack

Data Rack for optimum accessibility from all sides during assembly and installation, and a high degree of mobility when twin castors are used.







## **Features**

Model No.	DK 7391.000
Material	Profile frame, base/plinth: Carbon steel
	Feet: Die-cast zinc
General color	RAL 7035
Color	Profile frame, base/plinth: RAL 7035
	Panel, feet: RAL 5018
Supply includes	Torsionally rigid profile frame with 482.6 mm (19") holes
	Stable base/plinth with integral feet, with the option of floor
	anchoring without base trim panels
	Mounting Accessories
Dimensions	Width: 550 mm
	Height: 1,500 mm
	Depth: 750 mm
	Width: 21.7 "
	Height: 59.1 "
	Depth: 29.5 "
Height units	31 U
Height units	31 U

© Rittal 2025

## **Features**

Distance from the second mounting level, 50 mm hole pattern	150 - 350 mm 5.91 - 13.8 ″
Hole pattern between the mounting levels	50 mm 1.97 ″
Load capacity of the 19" levels	1,500 N
Note	Order second mounting level separately
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	16.781
Gross weight	17.664
PCF/VE (cradle-to-gate)	67.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177129795
E-Number Sweden	E7239646
ETIM 9	EC002507
ECLASS 8.0	27180602

© Rittal 2025 3