

Rittal – The System.

Faster – better – everywhere.



DK 7402.000

**Slide rail, 2 U, fixed installation,
continuous**

State: 2/22/2026 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7402.000 - Slide rail, 2 U, fixed installation, continuous for two 482.6 mm (19") mounting levels

For two 482.6 mm (19") mounting levels, to support heavy equipment on the Data Rack.

Features

Model No.	DK 7402.000
Product description	To support heavy equipment on the data rack. The preconfigured 350 mm mounting distance between the two mounting levels of the data rack corresponds exactly to the mounting dimensions of the slide rails. Alternatively, component shelves can be used to mount the components on a mounting level. These are available as a fixed installation as well as an extending version.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Load capacity	500 N, static
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19" Installation depth for components: 19 " Installation width for components: 19"
Packaging unit	2 pc(s).
Net weight	0.864 kg
Gross weight	1.072 kg
PCF/VE (cradle-to-gate)	4.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC000386
ECLASS 8.0	27400501

Features

Product description

DK Slide rail, continuous, For two 482.6 mm (19")-mounting angles (front+rear), For Data Rack