Rittal - The System.

Faster – better – everywhere.





DK 7451.000 Small Fiber Optic Distributors

State: 11/3/2025 (Source: rittal.com/us-en)



DK 7451.000 - Small Fiber Optic Distributors with mounting plate and splicing cassette accommodation

Small fiber optic distributor of fiberglass-reinforced polycarbonate with mounting plate and PG cable glands. Protection category IP 66.



Features

Model No.	DK 7451.000
Benefits	Mounting plate with variable accommodation for up to two splicing cassettes (cassette width variable from 92 to 120 mm) and integral anti-twist guard Dividing plate with comb strip for cable clamping, to cover the splicing cassette, and to accommodate 2 patch panels Cable entry via prepunched knockouts using cable glands (2 x 22.5 mm and 12 x 12.5 mm)
Material	Housing with cover: Fiberglass-reinforced polycarbonate Cover screws: Polyamide Insulating bungs: Polyamide Foamed-in PU seal
Color	RAL 7035
Supply includes	Housing with knockouts for cable glands Hinged cover with seal 2 cover screws, prepared for a lead seal Insulating bungs for wall mounting Mounting panel Dividing plate 12 cable glands M12 x 1.5 1 cable gland M20 x 1.5

© Rittal 2025

Features

Dimensions	Width: 180 mm Height: 254 mm Depth: 90 mm Width: 7.09 " Height: 10 " Depth: 3.54 "
Max. no. of fibers when using patch panels	24
Base material	Polycarbonate
Protection category IP to EN 60 529	IP 66
Packaging unit	1 pc(s).
Net weight	1.52
Gross weight	1.76
Customs tariff number	94032080
EAN	4028177130562
ETIM 9	EC002500
ECLASS 8.0	27180208

© Rittal 2025 3