

Rittal – The System.

Faster – better – everywhere.



DK 7480.300

Energy-Box, 482.6 mm (19")

State: 6/21/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7480.300 - Energy-Box, 482.6 mm (19") Pull-out

Designed to accommodate both DC and AC components, pull-out component facia affords optimum access to the wiring compartment from above and below.

Features

| | |
|--------------------------|---|
| Model No. | DK 7480.300 |
| Product description | Depth-variable top hat rail for "snap-in" fastening of installed equipment to DIN 43 880 sizes 1 – 3 (e.g. to accommodate flush-type outlets, circuit breakers, etc. or entire installation groups). Rear cable clamping. Two power distribution rails with connection terminals on insulated base. Plastic cover including reserve panel cover. To accommodate a maximum of 22 TE (22 x 18 mm = 396 mm). Housing height: 3 U. Housing depth: 223 mm. Maximum dimensions when pulled out: 220 mm. Connection terminals: 4 35 mm ² terminals, 18 16 mm ² terminals (per rail). |
| Color | RAL 7035 |
| Supply includes | Energy box with plastic blanking covers. Terminal 18 connection clamps, 16 mm ² 4 connection clamps, 35 mm ² Strain relief Identification strips Brush strip |
| Max. pitch units @ 18 mm | 22 |
| Dimensions | Width: 482.6 mm Depth: 220 mm Width: 19 " Depth: 8.66 " |
| Height units | 3 U |
| Packaging unit | 1 pc(s). |
| Net weight | 6.1 kg |
| Gross weight | 6.14 kg |
| Customs tariff number | 94032080 |

Features

| | |
|---------------------|---|
| ETIM 9 | EC002006 |
| ECLASS 8.0 | 27189268 |
| Product description | DK Energy-Box, 482.6 mm (19"), Pull-out |
