

# Rittal – The System.

Faster – better – everywhere.



## DK 7507.100

### FlatBox

State: 2/1/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



FRIEDHELM LOH GROUP

# DK 7507.100 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.



## Features

Model No.	DK 7507.100
Version	with 19" mounting rails
Product description	For flexible use as a wall-mounted or floor-standing enclosure.
Benefits	Tool-free quick mounting System accessories on the open 19" frame
Material	Carbon steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035

# Features

Supply includes	Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door catch freely selectable Connection components for tool-free, fast assembly Grounding kit for system-compatible grounding of all enclosure parts 19" profile rails
Height units	6 U
Dimensions	Width: 600 mm Height: 358 mm Depth: 600 mm Width: 23.6 " Height: 14.1 " Depth: 23.6 "
Installation height for components	6 U
Load capacity	max. 300 N
Note	Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210°
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	22.5
Gross weight	23
PCF/VE (cradle-to-gate)	91.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177551435
E-Number Sweden	E7239531

## Features

---

ETIM 9 EC002500

---

ETIM 8 EC002500

---

ECLASS 8.0 27180208

## Approvals

---

Explanations Manufacturer's declaration