

# Rittal – The System.

Faster – better – everywhere.



## DK 7507.740 Leveling Feet

State: 5/23/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7507.740 - Leveling Feet for FlatBox, M10 x 20 mm

Leveling Feet for FlatBox

## Features

Model No.	DK 7507.740
Product description	For screw-fastening into the enclosure base. Width across flats 17, fastening screw thread multi-tooth 30.
Applications	Instrument Cases Floor-Standing Housing
Function principle	For screw-fastening into the enclosure base
Material	Base: Plastic
Color	Base: RAL 9005
Levelling low	30 mm 1.18 "
Adjustment tool	Hex wrench, width across flats 0.67" (17 mm)
Max. load capacity (static) per component	5,500 N 1,236.449 lbf.
Dimensions	Thread: M10 Thread length: 20 mm Thread: M10 Thread length: 0.79 "
Leveling range	10 - 20 mm 0.39 - 0.79 "
Packaging unit	4 pc(s).
Net weight	0.128 kg
Gross weight	0.131 kg
Customs tariff number	39232100
ETIM 9	EC002620
ECLASS 8.0	27189261

# Features

---

Product description

DK Levelling feet, For screw-fastening onto the enclosure base,  
M10x20 mm, For Flatbox,