

Rittal – The System.

Faster – better – everywhere.



DK 7507.740 Leveling Feet

State: 7/13/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7507.740 - Leveling Feet for FlatBox, M10 x 20 mm

Leveling Feet for FlatBox

Features

| | |
|---|--|
| Model No. | DK 7507.740 |
| Product description | For screw-fastening into the enclosure base. Width across flats 17, fastening screw thread multi-tooth 30. |
| Applications | Instrument Cases Floor-Standing Housing |
| Function principle | For screw-fastening into the enclosure base |
| Material | Base: Plastic |
| Color | Base: RAL 9005 |
| Levelling low | 30 mm 1.18 ~ |
| Adjustment tool | Hex wrench, width across flats 0.67" (17 mm) |
| Max. load capacity (static) per component | 5,500 N 1,236.449 lbf. |
| Dimensions | Thread: M10 Thread length: 20 mm Thread: M10 Thread length: 0.79 ~ |
| Leveling range | 10 - 20 mm 0.39 - 0.79 ~ |
| Packaging unit | 4 pc(s). |
| Net weight | 0.128 |
| Gross weight | 0.131 |
| Customs tariff number | 73181900 |
| EAN | 4028177552678 |
| ETIM 9 | EC002620 |

Features

ECLASS 8.0

27189261