

Rittal – The System.

Faster – better – everywhere.



TE 7526.834 Module Plates

State: 6/5/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7526.834 - Module Plates for TE

The base area of the TE can be varied as required using the module plates.

Features

Model No.	TE 7526.834
Version	Vented
Product description	The base area of the TE can be varied as required using the module plates.
Applications	Please note the following when selecting the base plates: Enclosure width minus 150 mm Enclosure depth minus 50 mm
Material	Carbon steel, zinc-plated
Supply includes	Assembly components
Dimensions	Width: 650 mm Depth: 200 mm Width: 25.6 " Depth: 7.87 "
Suitable for	Enclosure type: TE Width: 800 mm Enclosure type: TE Width: 31.5 "
Packaging unit	1 pc(s).
Net weight	0.82 kg
Gross weight	1.02 kg
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	TE Module plate, WxD: 650x200 mm, Vented, For W: 800 mm