
Rittal – The System.

Faster - better - everywhere.





DK 7545.000 Ground rail, vertical

State: 11/4/2025 (Source: rittal.com/us-en)



DK 7545.000 - Ground rail, vertical for VX, VX IT

The supplied ground conductors facilitate star grounding of cable clamp straps on patch panels, ground terminals are fully adjustable, rail current carrying capacity approx. 200 A.

Features

Model No.	DK 7545.000	
Product description	Easy to mount on 25 mm DIN hole pattern on distributor or on 482.6 mm (19") punched rails. The supplied ground conductors facilitate star grounding of cable clamp straps on patch panels. The ground terminals are fully adjustable. Rail current carrying capacity approx. 200 A.	
Supply includes	Ground rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, x 5 mm null 15 grounding leads 6 mm², L = 500 mm Assembly components	
Dimensions	Length: 1,345 mm Length: 53 ″	
Suitable for	Enclosure type: VX VX IT TS Height: 1,600 mm Enclosure type: VX VX IT TS Height: 63 "	
Packaging unit	1 pc(s).	
Net weight	2.112	
Gross weight	2.312	
Copper weight (kg per piece)	0.87	
Customs tariff number	74198090	
EAN	4028177131873	

© Rittal 2025 2

Features

ETIM 9	EC000329	
ECLASS 8.0	27400605	

© Rittal 2025 3