Rittal – The System.

Faster – better – everywhere.




DK 7547.000


Ground rail, vertical

State: 11/15/2026 (Source: www.rittal.com/us-en)

DK 7547.000 - Ground rail, vertical for VX, VX IT

The supplied ground conductors facilitate star grounding of cable clamp straps on patch panels, ground terminals are fully adjustable, rail current carrying capacity approx. 200 A.





Features

Model No.	DK 7547.000
Product description	Easy to mount on 25 mm DIN hole pattern on distributor or on 482.6 mm (19") punched rails. The supplied ground conductors facilitate star grounding of cable clamp straps on patch panels. The ground terminals are fully adjustable. Rail current carrying capacity approx. 200 A.
Supply includes	Ground rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, 15 x 5 mm null 15 grounding leads 6 mm², L = 500 mm Assembly components
Dimensions	Length: 1,745 mm Length: 68.7 ″
Suitable for	Enclosure type: VX VX IT TS Height: 2,000 mm Enclosure type: VX VX IT TS Height: 78.7 ″
Packaging unit	1 pc(s).

Features

Net weight	2.4 kg
Gross weight	2.62 kg
Customs tariff number	74198090
ETIM 9	EC000329
ECLASS 8.0	27400605
Product description	DK earth rail, vertical, L: 1745 mm, grounding lead: 15x 6 mm², L: 500 mm, conductor terminals: 16x 2.5-16 mm²

© Rittal 2026