## Rittal – The System.

Faster – better – everywhere.





# DK 7641.000 AE Wall-Mounted Housings

State: 10/24/2025 (Source: rittal.com/us-en)



# DK 7641.000 - AE Wall-Mounted Housings with 19" (482.6 mm) profile rails, depth-variable

Wall-mounted housing for small networks with fixed 19" mounting level and flange plate with brush strip for cable entry at the bottom. Protection category IP 55.

#### **Features**

Model No.	DK 7641.000
Product description	Wall-mounted housing for small networks with a high protection category.
Material	Housing: Carbon steel
Surface finish	Housing: Powder-coated
	Profile rails: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door
	Door hinged on the right, may be swapped to the left
	Cam lock with 3 mm double-bit insert
	Flange plate with brush strip for cable entry in the enclosure base
	Profile rails, 482.6 mm (19"), fully depth adjustable
	C rail, for cable clamping on the rear panel
	Metal bracket for optional accommodation of a ground rail or a 19"
	socket strip
Height units	8 U
Dimensions	Width: 600 mm
	Height: 380 mm
	Depth: 350 mm
	Width: 23.6 "
	Height: 15 "
	Depth: 13.8 "
Installation depth	310 mm
	12.2 ″
Installation height for components	8 U
	right, may be swapped to the left

© Rittal 2025

### Features

No. of locks	1
Base material	Carbon steel
Protection category IP to EN 60 529	Up to IP 66 (depending on the selected flange plate)
Gland plate	Size: 5 Qty.: 1
Packaging unit	1 pc(s).
Net weight	17.23
Gross weight	18.137
Customs tariff number	94032080
EAN	4028177147027
E-Number Sweden	E7239953
ECLASS 8.0	27180208

# **Approvals**

Approvals	TÜV
	VDE

© Rittal 2025 3