

# Rittal – The System.

Faster – better – everywhere.



## DK 7641.000

## AE Wall-Mounted Housings

State: 12/18/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7641.000 - AE Wall-Mounted Housings with 19" (482.6 mm) profile rails, depth-variable

Wall-mounted housing for small networks with fixed 19" mounting level and flange plate with brush strip for cable entry at the bottom. Protection category IP 55.

## Features

|                                    |   |
|------------------------------------|---|
| Model No.                          | DK 7641.000   |
| Product description                | Wall-mounted housing for small networks with a high protection category.  |
| Material                           | Housing: Carbon steel   |
| Surface finish                     | Housing: Powder-coated<br>Profile rails: Zinc-plated  |
| Color                              | RAL 7035  |
| Supply includes                    | Housing with hinged door<br>Door hinged on the right, may be swapped to the left<br>Cam lock with 3 mm double-bit insert<br>Flange plate with brush strip for cable entry in the enclosure base<br>Profile rails, 482.6 mm (19"), fully depth adjustable<br>C rail, for cable clamping on the rear panel<br>Metal bracket for optional accommodation of a ground rail or a 19" socket strip |
| Height units                       | 8 U   |
| Dimensions                         | Width: 600 mm<br>Height: 380 mm<br>Depth: 350 mm<br>Width: 23.6 "<br>Height: 15 "<br>Depth: 13.8 "  |
| Installation depth                 | 310 mm<br>12.2 "  |
| Installation height for components | 8 U   |
| Position door catch                | right, may be swapped to the left   |

# Features

|                                    |  |
|------------------------------------|--|
| No. of locks                       | 1  |
| Base material                      | Carbon steel   |
| Protection category IP to EN 60529 | Up to IP 66 (depending on the selected flange plate) |
| Gland plate                        | Size: 5<br>Qty.: 1                                   |
| Packaging unit                     | 1 pc(s).   |
| Net weight                         | 17.23  |
| Gross weight                       | 18.137   |
| Customs tariff number              | 94032080   |
| EAN                                | 4028177147027  |
| E-Number Sweden                    | E7239953   |
| ECLASS 8.0                         | 27180208   |

# Approvals

|           |            |
|-----------|------------|
| Approvals | TÜV<br>VDE |
|-----------|------------|