

# Rittal – The System.

Faster – better – everywhere.



## DK 7643.000

# AE Wall-Mounted Housings

State: 4/6/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7643.000 - AE Wall-Mounted Housings with 19" (482.6 mm) profile rails, depth-variable

Wall-mounted housing for small networks with fixed 19" mounting level and flange plate with brush strip for cable entry at the bottom. Protection category IP 55.

## Features

Model No.	DK 7643.000
Product description	Wall-mounted housing for small networks with a high protection category.
Material	Housing: Carbon steel
Surface finish	Housing: Powder-coated Profile rails: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door Door hinged on the right, may be swapped to the left Cam lock with 3 mm double-bit insert Flange plate with brush strip for cable entry in the enclosure base Profile rails, 482.6 mm (19"), fully depth adjustable C rail, for cable clamping on the rear panel Metal bracket for optional accommodation of a ground rail or a 19" socket strip
Height units	13 U
Dimensions	Width: 600 mm Height: 600 mm Depth: 350 mm Width: 23.6 " Height: 23.6 " Depth: 13.8 "
Installation depth	310 mm 12.2 "
Installation height for components	13 U
Position door catch	right, may be swapped to the left

## Features

---

No. of locks	2
Base material	Carbon steel
Protection category IP to EN 60529	Up to IP 66 (depending on the selected flange plate)
Gland plate	Size: 5 Qty.: 1
Packaging unit	1 pc(s).
Net weight	23.399 kg
Gross weight	25 kg
Customs tariff number	94032080
ECLASS 8.0	27180208
Product description	DK Wall-mounted enclosures AE, WHD:600x600x350 mm, 13 U, AE 1360

## Approvals

---

Approvals	TÜV VDE
-----------	------------