

Rittal – The System.

Faster – better – everywhere.



DK 7643.000

AE Wall-Mounted Housings

State: 6/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7643.000 - AE Wall-Mounted Housings with 19" (482.6 mm) profile rails, depth-variable

Wall-mounted housing for small networks with fixed 19" mounting level and flange plate with brush strip for cable entry at the bottom. Protection category IP 55.

Features

| | |
|------------------------------------|---|
| Model No. | DK 7643.000 |
| Product description | Wall-mounted housing for small networks with a high protection category. |
| Material | Housing: Carbon steel |
| Surface finish | Housing: Powder-coated Profile rails: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Housing with hinged door Door hinged on the right, may be swapped to the left Cam lock with 3 mm double-bit insert Flange plate with brush strip for cable entry in the enclosure base Profile rails, 482.6 mm (19"), fully depth adjustable C rail, for cable clamping on the rear panel Metal bracket for optional accommodation of a ground rail or a 19" socket strip |
| Height units | 13 U |
| Dimensions | Width: 600 mm Height: 600 mm Depth: 350 mm Width: 23.6 " Height: 23.6 " Depth: 13.8 " |
| Installation depth | 310 mm 12.2 " |
| Installation height for components | 13 U |
| Position door catch | right, may be swapped to the left |

Features

| | |
|------------------------------------|--|
| No. of locks | 2 |
| Base material | Carbon steel |
| Protection category IP to EN 60529 | Up to IP 66 (depending on the selected flange plate) |
| Gland plate | Size: 5 Qty.: 1 |
| Packaging unit | 1 pc(s). |
| Net weight | 23.399 kg |
| Gross weight | 25 kg |
| Customs tariff number | 94032080 |
| ECLASS 8.0 | 27180208 |
| Product description | DK Wall-mounted enclosures AE, WHD:600x600x350 mm, 13 U, AE 1360 |

Approvals

| | |
|-----------|------------|
| Approvals | TÜV VDE |
|-----------|------------|