

Rittal – The System.

Faster – better – everywhere.



DK 7645.000

AE Wall-Mounted Housings

State: 8/3/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7645.000 - AE Wall-Mounted Housings with 19" (482.6 mm) profile rails, depth-variable

Wall-mounted housing for small networks with fixed 19" mounting level and flange plate with brush strip for cable entry at the bottom. Protection category IP 55.

Features

Model No.	DK 7645.000
Product description	Wall-mounted housing for small networks with a high protection category.
Material	Housing: Carbon steel
Surface finish	Housing: Powder-coated Profile rails: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door Door hinged on the right, may be swapped to the left Cam lock with 3 mm double-bit insert Flange plate with brush strip for cable entry in the enclosure base Profile rails, 482.6 mm (19"), fully depth adjustable C rail, for cable clamping on the rear panel Metal bracket for optional accommodation of a ground rail or a 19" socket strip
Height units	16 U
Dimensions	Width: 600 mm Height: 760 mm Depth: 350 mm Width: 23.6 " Height: 29.9 " Depth: 13.8 "
Installation depth	310 mm 12.2 "
Installation height for components	16 U
Position door catch	right, may be swapped to the left

Features

No. of locks	2
Base material	Carbon steel
Protection category IP to EN 60529	Up to IP 66 (depending on the selected flange plate)
Gland plate	Size: 5 Qty.: 1
Packaging unit	1 pc(s).
Net weight	29.7
Gross weight	30.1
Customs tariff number	94032080
EAN	4028177147041
E-Number Sweden	E7239955
ETIM 9	EC002500
ECLASS 8.0	27180208

Approvals

Approvals	TÜV VDE
-----------	------------