

Rittal – The System.

Faster – better – everywhere.



DK 7688.000
19" profile rails

State: 2/10/2026 (Source: rittal.com/us-en)

DK 7688.000 - 19" profile rails for DK PS, CS New Basic housings

For installing 19" components in network and server racks and in CS New Basic outdoor housings

Features

Model No.	DK 7688.000
Product description	For installing 19" components in DK PS network and server racks and in CS New Basic outdoor housings. The profile rails are depth-adjustable in the 25 mm hole pattern. An installation bracket is required to mount the profile rails.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Mounting accessories
Height units	24 U
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19" Installation depth for components: 19 " Installation width for components: 19"
Suitable for	Enclosure type: CS basic housings DK PS Height: = 1,200 mm Enclosure type: CS basic housings DK PS Height: = 47.2 "
Packaging unit	2 pc(s).
Net weight	2.494
Gross weight	2.693
PCF/VE (cradle-to-gate)	10.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

Features

Customs tariff number 73269098

EAN 4028177133341

ETIM 9 EC002620

ECLASS 8.0 27189261