


# Rittal – The System.

Faster – better – everywhere.



## DK 7709.135

## Wall-mounted enclosures EL, 3-part

State: 7/31/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7709.135 - Wall-mounted enclosures EL, 3-part with punched rails and profile rails, depth-variable

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top and bottom, punched rails, C rails, wall mounting bracket. Protection category IP 55.

## Features

|                     |  |
|---------------------|--|
| Model No.           | DK 7709.135  |
| Version             | Wall-mounted housing IT<br>with punched rails and profile rails, depth-variable  |
| Product description | Wall-mounted enclosure with hinged door provides optimum accessibility.  |
| Material            | Wall and hinged part: Carbon steel, 1.5 mm<br>Viewing window: Single-pane safety glass, 3 mm   |
| Surface finish      | Powder-coated  |
| General color       | RAL 7035   |
| Color               | Wall and hinged part: RAL 7035<br>Viewing door: RAL 7035/7015 (slate gray)   |
| Supply includes     | Wall section closed at top and bottom with flange (gland) plate, two vertical mounting rails and horizontal C-profile rails for cable clamping.<br>Hinged part with 25 mm pitch pattern in the front and rear frame, two 482.6 mm (19") profile angles at the front, fully depth adjustable<br>4 wall mounting brackets 10 mm<br>Designer viewing door<br>1 enclosure key double bit no. 5<br>Mini-comfort handle for lock inserts<br>Security lock 3524 E |
| Height units        | 9 U  |

# Features

|                                       |  |
|---------------------------------------|--|
| Dimensions                            | Width: 600 mm<br>Height: 478 mm<br>Depth: 473 mm<br>Width: 23.6 "<br>Height: 18.8 "<br>Depth: 18.6 "       |
| Installation depth                    | 420 mm<br>16.5 "   |
| Clearances                            | Clearance width: 502 mm<br>Clearance height: 415 mm<br>Clearance width: 19.8 "<br>Clearance height: 16.3 " |
| Depth hinged part                     | 316 mm<br>12.4 "   |
| Depth of wall section                 | 135 mm<br>5.31 "   |
| IK code                               | IK08   |
| Load capacity of hinged part (static) | 450 N<br>101.164 lbf.  |
| Base material                         | Carbon steel   |
| Protection category IP to EN 60 529   | IP 55  |
| Packaging unit                        | 1 pc(s).   |
| Net weight                            | 29.45  |
| Gross weight                          | 31   |
| Customs tariff number                 | 94032080   |
| EAN                                   | 4028177324183  |
| ETIM 9                                | EC000261   |
| ECLASS 8.0                            | 27142408   |

# Approvals

---

Approvals

UL + C-UL (listed)