

**Rittal – The System.**

Faster – better – everywhere.



**DK 7712.135**

**Wall-mounted enclosures EL, 3-part**

State: 4/27/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7712.135 - Wall-mounted enclosures EL, 3-part with punched rails and profile rails, depth-variable

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top and bottom, punched rails, C rails, wall mounting bracket. Protection category IP 55.

## Features

Model No.	DK 7712.135
Version	Wall-mounted housing IT with punched rails and profile rails, depth-variable
Product description	Wall-mounted enclosure with hinged door provides optimum accessibility.
Material	Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General color	RAL 7035
Color	Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section closed at top and bottom with flange (gland) plate, two vertical mounting rails and horizontal C-profile rails for cable clamping. Hinged part with 25 mm pitch pattern in the front and rear frame, two 482.6 mm (19") profile angles at the front, fully depth adjustable 4 wall mounting brackets 10 mm Designer viewing door 1 enclosure key double bit no. 5 Mini-comfort handle for lock inserts Security lock 3524 E
Height units	12 U

# Features

Dimensions	Width: 600 mm Height: 612 mm Depth: 473 mm Width: 23.6 " Height: 24.1 " Depth: 18.6 "
Installation depth	420 mm 16.5 "
Clearances	Clearance width: 502 mm Clearance height: 549 mm Clearance width: 19.8 " Clearance height: 21.6 "
Depth hinged part	316 mm 12.4 "
Depth of wall section	135 mm 5.31 "
IK code	IK08
Load capacity of hinged part (static)	600 N 134.885 lbf.
Base material	Carbon steel
Protection category IP to EN 60 529	IP 55
Packaging unit	1 pc(s).
Net weight	34.2 kg
Gross weight	36 kg
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27142408
Product description	DK Wall-mounted enclosures, 3-part, WHD: 600x612x473 mm, 12 U, With punched rails, and mounting angles, depth-variable

# Approvals

---

Approvals

UL + C-UL (listed)