Rittal - The System.

Faster – better – everywhere.





DK 7715.535 Wall-mounted enclosures EL, 3-part

State: 11/29/2025 (Source: rittal.com/us-en)



DK 7715.535 - Wall-mounted enclosures EL, 3-part preconfigured with profile rails, depth-variable

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top, with brush strip at the bottom, mounting rails, C rails, outlet filter, ground rail, wall-mounting bracket

Features

Model No.	DK 7715.535
Version	Wall-mounted housing IT
	pre-configured with profile rails, depth-variable
Product description	Wall-mounted enclosure with hinged door provides optimum
	accessibility.
Material	Wall and hinged part: Carbon steel, 1.5 mm
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General color	RAL 7035
Color	Wall and hinged part: RAL 7035
	Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section with solid gland plate at the top and brush strip at the
	bottom, two vertical mounting rails and C rail, horizontal, for cable clamping
	Hinged part with 25 mm pitch pattern in the front and rear frame,
	two 482.6 mm (19") profile angles at the front, fully depth adjustable
	and side outlet filters on left and right
	Ground rail with star grounding
	Designer viewing door
	1 enclosure key double bit no. 5
	Wall mounting brackets, 10 mm, reinforced
	Mini-comfort handle for lock inserts
	Security lock 3524 E
Height units	15 U

© Rittal 2025 2

Features

Dimensions	Width: 600 mm
	Height: 746 mm
	Depth: 673 mm Width: 23.6 "
	Height: 29.4 "
	Depth: 26.5 "
	Берин. 20.0
Installation depth	620 mm
	24.4 "
Clearances	Clearance width: 502 mm
	Clearance height: 683 mm
	Clearance width: 19.8 ″
	Clearance height: 26.9 "
Depth hinged part	516 mm
	20.3 ″
Depth of wall section	135 mm
	5.31 ″
IK code	IK08
Load capacity of hinged part	750 N
(static)	168.607 lbf.
Base material	Carbon steel
Protection category IP to EN 60 529	IP 54 in conjunction with solid gland plate top and bottom
Packaging unit	1 pc(s).
Net weight	45.6
Gross weight	48.1
Customs tariff number	94032080
EAN	4028177551022
E-Number Sweden	E7239960
ETIM 9	EC000261
ECLASS 8.0	27142408

© Rittal 2025 3

Approvals

Approvals

UL + C-UL (listed)

© Rittal 2025 4