

Rittal – The System.

Faster – better – everywhere.



DK 7721.135

Wall-mounted enclosures EL, 3-part

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7721.135 - Wall-mounted enclosures EL, 3-part with punched rails and profile rails, depth-variable

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top and bottom, punched rails, C rails, wall mounting bracket. Protection category IP 55.

Features

Model No.	DK 7721.135
Version	Wall-mounted housing IT with punched rails and profile rails, depth-variable
Product description	Wall-mounted enclosure with hinged door provides optimum accessibility.
Material	Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General color	RAL 7035
Color	Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section closed at top and bottom with flange (gland) plate, two vertical mounting rails and horizontal C-profile rails for cable clamping. Hinged part with 25 mm pitch pattern in the front and rear frame, two 482.6 mm (19") profile angles at the front, fully depth adjustable 4 wall mounting brackets 10 mm Designer viewing door 1 enclosure key double bit no. 5 Security lock 3524 E Comfort handle for lock inserts and 2-point locking
Height units	21 U

Features

Dimensions	Width: 600 mm Height: 1,012 mm Depth: 473 mm Width: 23.6 " Height: 39.8 " Depth: 18.6 "
Installation depth	420 mm 16.5 "
Clearances	Clearance width: 502 mm Clearance height: 949 mm Clearance width: 19.8 " Clearance height: 37.4 "
Depth hinged part	316 mm 12.4 "
Depth of wall section	135 mm 5.31 "
IK code	IK08
Load capacity of hinged part (static)	750 N 168.607 lbf.
Base material	Carbon steel
Protection category IP to EN 60 529	IP 55
Packaging unit	1 pc(s).
Net weight	46.55 kg
Gross weight	49 kg
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27142408
Product description	DK Wall-mounted enclosures, 3-part, WHD: 600x1012x473 mm, 21 U, With punched rails, and mounting angles, depth-variable

Approvals

Approvals

UL + C-UL (listed)